



EVISA E200.R



The lubricated rotary vane pumps EVISA are designed to be used in a wide range of industrial and healthcare applications.

They can run continuously from atmospheric pressure to ultimate vacuum.

They are silent and extremely robust.

- Single stage vacuum pump
- Continuous operation from atmospheric pressure to end vacuum : $6 \cdot 10^{-2}$ mbar
- High pumping speed even at low pressure
- Integrated oil mist filter on the exhaust
- IE3 motor

Technical characteristics

		50 Hz	60 Hz
E200.R HV	Nominal flow rate $\text{m}^3 \cdot \text{h}^{-1} - \text{cfm}$	200 - 117,7	240 - 141,3
	PNEUROP pumping speed ⁽¹⁾ $\text{m}^3 \cdot \text{h}^{-1} - \text{cfm}$	190 - 111,8	228 - 134,2
	Pumping speed at 1 mbar inlet pressure ⁽¹⁾ $\text{m}^3 \cdot \text{h}^{-1} - \text{cfm}$	134 - 78,9	161 - 94,8
	Without gas ballast End vacuum mbar - torr	$\leq 6 \cdot 10^{-2} - 4,5 \cdot 10^{-2}$	$\leq 6 \cdot 10^{-2} - 4,5 \cdot 10^{-2}$
	Fully opened gas ballast		
E200.R	End vacuum mbar - torr	$\leq 1 - 0,75$	$\leq 1 - 0,75$
	Water vapor permitted maximum pressure mbar - torr	20,2 - 15,1	21,3 - 15,9
	Water vapor capacity $\text{kg} \cdot \text{h}^{-1}$	2,2	2,8
	Without gas ballast End vacuum mbar - torr	$\leq 3 - 2,3$	$\leq 3 - 2,3$
	Fully opened gas ballast		
End vacuum mbar - torr		$\leq 5 - 3,8$	$\leq 5 - 3,8$
Water vapor permitted maximum pressure mbar - torr		14 - 10,5	15 - 11,2
Water vapor capacity $\text{kg} \cdot \text{h}^{-1}$		1,5	2
100 % synthetic oil		MV99S	MV99S
Oil capacity $\text{l} - \text{qt}$		5 - 5,3	5 - 5,3
Noise level dB(A)		71	77

⁽¹⁾ Measurements according to PNEUROP 6602 specifications - 20°C


Versions

GEOGRAPHIC ZONE		EUROPE	ASIA MIDDLE-EAST	SOUTH AMERICA	USA	JAPAN
Electrical motor	Number of phases	3	3	3	3	3
	Voltage V	230 / 400	220 / 380	190 / 380	208-230 / 460	220 / 380
	Period Hz	50	60	50	60	50 / 60
	Motor power	4 kW	4,8 kW	4 kW	7,5 HP	4 / 4,8 kW
	Rotation speed min^{-1}	1500	1800	1500	1800	1500 / 1800
Inlet connection ⁽²⁾		2" BSP	2" BSP	2" NPT	2" NPT	2" BSP
Outlet connection ⁽²⁾		2" BSP	2" BSP	2" NPT	2" NPT	2" BSP
Weight with oil $\text{kg} - \text{lb}$		143 - 316	158 - 349	174 - 384	174 - 384	160 - 353

⁽²⁾ DN 50 ISO-KF connector can be supplied, see accessories

Lubricated rotary vane vacuum pumps

Dimensions mm (inch)



References

	E200.R HV		E200.R	
	WITH GAS BALLAST	WITHOUT GAS BALLAST	WITH GAS BALLAST	WITHOUT GAS BALLAST
EUROPE 3ph, 230/400V-50Hz	823766 + 624229	823766	823830 + 624229	823830
SOUTH AMERICA / USA 3ph, 190/380V-50Hz, 208-230/460V-60Hz	824060 + 624229	824060	Contact us	Contact us
ASIA / MIDDLE - EAST 3ph, 220/380V-50/60Hz	823835 + 624229	823835	823833 + 624229	823833
JAPAN Version : contact us				

Special versions

	E200.R HV		E200.R	
	WITH GAS BALLAST	WITHOUT GAS BALLAST	WITH GAS BALLAST	WITHOUT GAS BALLAST
CONDENSABLE VAPOUR PUMPING (small propeller) 3ph, 230/400V-50Hz	823864 + 624229	823864	823837 + 624229	823837
OXYGEN with Fomblin oil 3ph, 230/400V-50Hz	823873 + 624229	823873	823872 + 624229	823872
EVISA H₂O 3ph, 230/400V-50Hz	Contact us	Contact us	823845 + 624229	823845

For booster direct mounting : contact us

Maintenance kits

3 000 hour usual maintenance with silicone o'ring for oil mist filter	724054
3 000 hour usual maintenance with viton o'ring for oil mist filter	724055
12 000 hour preventive maintenance	724052
Gasket set	624230
3 000 hour usual maintenance for OXYGEN version	724089
12 000 hour preventive maintenance for OXYGEN version	724087



3 000 hour usual maintenance



12 000 hour preventive maintenance

Specifications are subject to be changed without notice.



Accessories and Options

1	Oil Level Safety (OLS) with float	624245
	Timer box for oil level safety (base mounting)	670810
	NC bimetal temperature safety - opening at 120°C + SNH - Max 24V	624246
	Oil Level Safety and PT100 temperature sensor	624247
	PT100 temperature sensor	624248
2	2" BSP suction filter	
	Paper cartridge	715350
	Polyester cartridge	715351
	Carbon cartridge	715352
	Vacuum gauge fitted on filter	617536
	2" BSP paper/paper double filtration 201PA + 201PA	670615
	2" BSP polyester/carbon double filtration 201PO + 201CH	670618
3	Liquid trap 200	
	340 m ³ .h ⁻¹	
	2" BSP	
	Aluminium head / polycarbonate cylinder / without float	724801
	Aluminium head / polycarbonate cylinder / with float	724802
	Stainless steel head / Pyrex cylinder / without float	724803
	Stainless steel head / Pyrex cylinder / with float	724804
	Pyrex bottle 250 ml under trap assembly	615441
	Pyrex bottle 500 ml under trap assembly	615442
	Pyrex bottle 1000 ml under trap assembly	615443
	Bracket for wall fixing	619907
	Electro-pneumatic automatic drain with control board	816002
	Electrical automatic drain with control board	816003
	Adjusting valve fitted on T-square	713842
	Vacuum hose (0,6 m) FF 2" BSP	618149
	Vacuum hose (1 m) FF 2" BSP	606099
	Vacuum hose (1,5 m) FF 2" BSP	607592
	Suction hose with non-return valve (1 m)	770154
	Exhaust double elbow mounting	622788
	Base frame assembly height 150 mm	670806
4	Elevated base frame	
	(H=525 mm)	
	For 1 pump	617612
	For 2 pumps	619545
	Without regulation contact 3-ph 400V	770499
Direct starter	Without regulation contact 3-ph 230V	770500
(wall mounting)	With regulation contact LG7 3-ph 400V	710426
	With regulation contact LG7 3-ph 230V	710434
	Control board with FLEXO solenoid valve 3-ph, 400V + N for warm up and degasing cycle	770815
	Control board with FLEXO solenoid valve 3-ph, 400V + N for degasing cycle	770822
	Aluminium adapter M2" / DN50 KF	117132
	Aluminium clamping collar DN50 KF	361640
	Centering ring stainless steel / VITON	361643
	Stainless steel hose (0,5 m) DN50 KF	361648
	Stainless steel hose (1 m) DN50 KF	361649



1 Oil Level Safety



2 suction filter
type 201




3 Liquid trap 200
with mechanical
stop and
optional bottle




4 Elevated base frame
for 2 pumps

Lubricated rotary vane vacuum pumps

Pumping speed on 1000 l vessel



Performance curves



— 60 Hz - without gas ballast
— 50 Hz - without gas ballast

--- 60 Hz - with opened gas ballast
--- 50 Hz - with opened gas ballast